



**3** JAHRE GARANTIE

## ANSMANN T600FRB

- High quality aluminum torch for professional use
  - Degree of protection: IPX4
  - Use of the latest LED technology from CREE
  - Powered by alkaline batteries or a 18650 Li-Ion battery - a matching cartridge for the Li-Ion battery is included
  - We recommend the use of ANSMANN 18650 Li-Ion batteries with safety circuit and raised positive pip
  - Stepless **Zoom** function by moving the lamp head from precise point light to even floodlight
  - Large on / off switch and grippy surface for maximum ease of use even with gloves on - ideal for one-handed operation
  - Five light functions: 100% / 25% / 10% / Strobe / SOS
  - Brightness: 620 lumens (100%), 260 lumens (25%) / 70 lumens (10%) with a beam range of up to 165 m
  - Includes 3 x AAA alkaline batteries, Li-Ion adapter and belt clip
- 3 years ANSMANN-Germany manufacturer warranty**

## INFORMATION

**Product name:** T600FRB  
**Article number:** 1600-0268  
**EAN-Code:** 4013674153732  
**Accessories incl.:** 3x Micro AAA Batteries, Beltclip, Li-Ion adapter

**Packing + Product:** 125 x 39 x 272mm 150g  
**Packing Unit:** 5  
**Available:** UK Stock  
**Customs tariff number:** 8513100000