

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2043650018](#)  
**Status:** **Active**  
**Overview:** Coeur CST High-Current Interconnect System  
**Description:** Coeur CST High-Current Female Surface Mount Socket, 3.40mm Diameter, with 1.00mm Float

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification 2043130018-PK-000 \(PDF\)](#)  
[Product Specification 2043130018-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification 2043130018-AS-000 \(PDF\)](#)

**General**

Product Family	PCB Receptacles
Series	<a href="#">204365</a>
Application	Power
Comments	Current and voltage performances are dependent upon application variables   Embossed Tape & Reel and Tray packaging available. Contact Molex for information., Current and voltage performances are dependent upon application variables   Embossed Tape & Reel and Tray packaging available. Contact Molex for information.
Datasheet Order No	987651-8619
Overview	<a href="#">Coeur CST High-Current Interconnect System</a>
Product Name	Coeur CST
UPC	191130519460

**Physical**

Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Net Weight	4.794/g
Number of Rows	1
Orientation	Vertical
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	N/A
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	600
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	205

**Material Info**



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -ED/88/2018 (15 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[204365 Series](#)

**Mates With**

Coeur CST 3.40mm Pin [203263](#)

**Reference - Drawing Numbers**

Application Specification	2043130018-AS-000
Packaging Specification	2043130018-PK-000
Product Specification	2043130018-PS-000
Sales Drawing	2043650018-SD-000

This document was generated on 07/26/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**