

HelaGuard Handipacks

- A range of Handipacks aimed at the contractor
- All packs have 10mts of conduit and 10 standard fittings
- Available in three types to cover most applications
- Two popular sizes of conduit for each type, to suit M20 and M25 fittings



Polypropylene - HG-PP

- Suitable for general purpose installations
- IP40 fittings
- Halogen free and good resistance to oils and greases



PA6 - HG - SW

- High specification PA6 in standard weight with IP66 fittings
- Halogen free and low smoke & toxicity
- Highly resistant to solvents, oils and abrasion



SPIRAL PVC - FPC

- Spiral reinforced PVC that is highly flexible, yet very tough and durable
- IP65 rating with high impact resistance
- Withstands torsional movement



Handipacks	
Order Code	Product Description
L0174	HG-PP21 Conduit x 10MTS & 10 x M20 Fittings
L0175	HG-PP26 Conduit x 10MTS & 10 x M25 Fittings
L0176	HG-SW21 Conduit x 10MTS & 10 x M20 Fittings
L0177	HG-SW25 Conduit x 10MTS & 10 x M25 Fittings
L0178	FPC20 Conduit x 10MTS & 10 x M20 Fittings
L0179	FPC25 Conduit x 10MTS & 10 x M25 Fittings