

R18N18G-0 | 18V Cordless 18G Nailer



- AirStrike™ Technology provides cordless convenience, eliminating the need for a noisy compressor, bulky air hose or expensive gas cartridges.
- Fires 18 Gauge (1.2mm) nails from 15 to 50mm long.
- 2 firing modes, full sequential mode for precision and contact actuation mode for rapid fastening.
- Grip-light technology engages twin LEDs by grasping the handle.
- Tool less depth of drive adjustment helps protect work surface and allows proper setting of nail heads.
- Dry-fire lockout prevents the tool working without nails loaded.
- Tool less jam release for easy removal of clear nails.

	R18N18G-0
Charger included?	No
Magazine angle	Straight
Magazine capacity brads	105
Nail capacity	15-50mm
Nail type (mm)	1.2
No. of batteries supplied	0
Power	18V
Sound power level [dB(A)]	94.0
Sound power level measured [dB(A)]	94
Sound power level measured uncertainty [dB(A)]	3
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	83.0
Sound pressure level uncertainty [dB(A)]	3.0
Standard equipment	500 x 32mm nails, 2 x no mar shoes, reversible belt hook
Supplied in	Recyclable Carton
Vibration level [m/s²]	1.5
Vibration nailing [m/s²]	1.5
Vibration nailing uncertainty [m/s²]	1.5
Vibration uncertainty [m/s²]	1.5
Weight [without battery] [Kg]	2.5
Weight with battery pack (kg)	2.9