

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1202530360](#)  
**Status:** **Active**  
**Overview:** [Contrinex Inductive and Photoelectric](#)  
**Description:** Contrinex Inductive Sensor, M8 Housing, 2mm Operating Distance, Embeddable, PNP, NO, 3-pin M8 Connector, 45mm Housing Length

**Documents:**

[Product Specification 1202530360-000 \(PDF\)](#)      [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Sensors
Series	<a href="#">120253</a>
Exclude SD Check	Yes
IP Rating	IP67
Overview	<a href="#">Contrinex Inductive and Photoelectric</a>
Product Category	Sensors
Product Literature Order No	987651-9402
Product Name	Contrinex
Type	Inductive
UPC	191130065851

**Physical**

Connection	Connector (M8, 3-pin)
Length	45mm
Material - Housing	Stainless Steel
Material - Sensing Face	PA12
Mounting Style	Embeddable
Operating Distance	2mm
Output	NO
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +70°C

**Electrical**

Polarity	PNP
Switching Frequency	≤ 5000 Hz

**Material Info**

Engineering Number	DW-AS-623-M8-001
--------------------	------------------

**Reference - Drawing Numbers**

Product Specification	1202530360-000
-----------------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[120253 Series](#)