

Technical Data

Part Number: X4C5000VM-W

Product Group: CCTV

Product Type: IP Dome Camera



Xvision 5MP H265+ Vandal Dome IP Camera, 2.7-12mm Motorised Lens, 60m IR, Starlight

Model: X4C5000VM-W	
Style	Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, Starlight, Backlight Compensation, Privacy
Resolution	5MP
Lens Type	Motorised
Lens Size	2.7-12mm

Technical Data

Viewing Angle	34-116°
Night Vision	60m IR
Minimum Illumination	0.05 Lux
Video Compression	H265+
Video Streams	Dual Stream
Video Resolution & Frame Rates	2592x1944 - 15fps 2592x1520 - 20fps 2048x1520 - 25fps 1920x1080 - 25fps 1280x720 - 25fps
Video Bitrate	8Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<7W
Audio Input	Yes
Power Input	12V DC Socket (2.1mm)
On Board Recording	No
Alarm Input	Yes
Video Analytics	No
Operating Temperature	-30 ~ 55°
Dimensions (WHD)	Ø135.4x127.7mm
Weight (kg)	0.72
Warranty	3 Year Warranty