LQH43NH102J03# "#" indicates a package specification code.

















< List of part numbers with package codes > LQH43NH102J03L , LQH43NH102J03K

Shape





Notes

When rated current is applied to the products, self-temperature rise shall be limited to 20 $^{\circ}$ C max and inductance will be within $\pm 10\%$ of nominal value.

References

Packaging code	Specifications	Minimum quantity
L	φ180mm Embossed taping	500
K	φ330mm Embossed taping	2500

	Mass (Typ.)	
1 piece		0.13g

Specifications

Inductance	1000μH ±5%
Inductance test frequency	1kHz
Rated current (Itemp) (Based on Temperature rise)	45mA
Max. of DC resistance	18.6Ω
Avg. of DC resistance	15.5Ω±20%
Q (min.)	40
Q test frequency	252kHz
Self resonance frequency (min.)	2MHz
Operating temperature range	-40 to 125°C
Class of magnetic shield Series	No Shield LQH43NH_03

1 of 1



^{1.} This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



^{2.} This datasheet has only typical specifications because there is no space for detailed specifications