



**45W**  
45W DRIVER FOR LED PANEL

SKU:6004

**2** YEARS  
WARRANTY

## Technical Information

Output Voltage: DC:30-42V

Watts: 45

Input Current: 0.25A

Output Current: 1050mA

Body Type: ABS Plastic

IP Rating: IP20

Dimmable: No

Warranty (Years): 2

Operation Temperature: -25 to +50°C

Input Power: AC:200-240V,50/60Hz

## Features

- ✓ Easy to Install
- ✓ Suitable with V-TAC Panels(Fixture Not Included)
- ✓ Application - Office, Conference Room, Schools, Lobby, Cabin, Kitchen etc

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.35
Length(Box)mm	115
Width(Box)mm	40
Height(Box)mm	70
Unit CBM	0.000378

## Listing Details

EAN Code	3800230628275
Commodity Code	8504409090

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	2700

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES