

CyberPower

CP750LCD INTELLIGENT LCD UPS

Offering advanced energy-saving battery backup and surge protection against power surges and interruptions.

The CyberPower Intelligent LCD Series CP750LCD uninterruptible power supply (UPS) safeguards PCs and other electronics (monitors, cable/DSL modems, VoIP routers, and home theater devices) from blackouts, brownouts, surges, spikes, sags, and other power abnormalities.

This UPS system utilizes GreenPower UPS™ high-efficiency design to save on energy costs by reducing energy consumption and heat buildup. The multifunction diagnostic LCD provides users the ability to check UPS operating status and assist in trouble-shooting power anomalies.

A Three-Year Warranty ensures that this UPS has passed our highest quality standards in design, assembly, material or workmanship and further protection is offered by a \$150,000 Connected Equipment Guarantee.



TYPICAL APPLICATIONS

- Desktop Computers
- Home Networking/VoIP
- Personal Electronics
- Home Theater Device

FEATURES

- 750VA / 420W
- Standby Topology
- Multifunction LCD Screen
- GreenPower UPS™
- Full-time Surge Protection and Battery Backup
- Desktop Form Factor
- 8 Outlets / USB Port / RJ11 Protection
- PowerPanel® Personal Edition
- 3-Year Warranty

SPECIFICATIONS

GENERAL

UPS Topology	Standby
Energy Saving	GreenPower UPS™ High Efficiency

INPUT

Voltage	120 VAC
Frequency Range	47 - 63 Hz
Plug Type	NEMA 5-15P

CP750LCD INTELLIGENT LCD UPS



SPECIFICATIONS - CONT.

INPUT - CONT.

Plug Style	Right Angle - 45° Offset
Cord Length	5'

OUTPUT

VA	750 VA
Watts	420 W
On Battery Voltage	120 VAC \pm 5%
On Battery Frequency	50/60 Hz \pm 1%
On Battery Waveform	Simulated Sine Wave
Outlet Type	NEMA 5-15R
Outlets - Total	8
Outlets - Battery & Surge Protected	4
Outlets - Surge-Only Protected	4
Outlets - Widely Spaced	2
Overload Protection	Internal Circuitry Limiting Circuit Breaker

BATTERY

Runtime at Half Load (min)	10
Runtime at Full Load (min)	3
Battery Type	Sealed Lead-Acid
Battery Size	12V/7Ah
Battery Quantity	1
Typical Recharge Time	8 hours

SURGE PROTECTION & FILTERING

Surge Suppression	890 Joules
Phone Protection RJ11	1-In, 2-Out
EMI/RFI Filtration	Yes

MANAGEMENT & COMMUNICATIONS

Multifunction LCD Panel	Yes
HID Compliant USB Port	Yes
Management Cable	USB Cable
LED Indicators	Power On, Wiring Fault
Audible Alarms	On Battery, Low Battery, Overload
Software	PowerPanel® Personal Edition

PHYSICAL

Form Factor	Compact
Keyhole Mounting Slots	Yes
Dimensions - W×H×D (in)	10.4 × 6.9 × 3.1
Weight (lbs)	6.7

ENVIRONMENTAL

Operating Temperature	32 - 104 °F (0 - 40 °C)
Operating Humidity	0 - 90% (non-condensing)

CERTIFICATIONS

Safety	UL1778, cUL CSA C22.2 No. 107.3, FCC DOC Class B
Environmental	RoHS Compliant

WARRANTY

Product Warranty	3 Years
Connected Equipment Guarantee	Lifetime
CEG Amount	\$150,000