


Conn.1 USB3.0 A Type Male



Conn.2 USB3.0	A Type Female	-

CUSTOMER

Ø

mm

			TOLERANCE	SIGNA	ΓURES	DATE	PRO-SIGNAL		
			0 - 10 ±0.05 10 - 99 ±0.5	DRAFT:WU J	IA XIN	2019-9-25			
REV	PART NO.& SAMPLE NO.	BY	10 - 99 ±0.5 100 - 999 ±10.0 1000 - 9999 ±100.00 10000 - 99999 ±1000.00	CHECKEO:					
	CS32880		\oplus	APPROVAL:				USB A Male — USB A Female, V3.0	
			SHEET	SCALE	UNIT	REV	TITLE		

OF

1:1