

Technical Specifications

Coloured Neodymium Pot Magnets

No.	Product Image	Diameter (mm)	Thickness (mm)	Hole Size (mm)	Screw Head (mm)	Pull Force (kg)	Pack QTY
1		16	5.2	3.5	6.5	6	PK10
2		20	7.2	4.5	8.6	9	PK10
3		25	7.7	5.5	10.6	19	PK10
4		32	7.8	5.5	10.6	32	PK10
5		40	7.8	6.5	12	52	PK5
6		48	10.8	8.5	19	75	PK1
7		60	15	8.5	19	115	PK1

Black	White	Red	Gold	Blue	Green	Purple
E1100/NEO/BLK/F	E1100/NEO/W/F	E1100/NEO/R/F	E1100/NEO/GO/F	E1100/NEO/B/F	E1100/NEO/G/F	E1100/NEO/P/F
E1101/NEO/BLK/F	E1101/NEO/W/F	E1101/NEO/R/F	E1101/NEO/GO/F	E1101/NEO/B/F	E1101/NEO/G/F	E1101/NEO/P/F
E1102/NEO/BLK/F	E1102/NEO/W/F	E1102/NEO/R/F	E1102/NEO/GO/F	E1102/NEO/B/F	E1102/NEO/G/F	E1102/NEO/P/F
E1103/NEO/BLK/F	E1103/NEO/W/F	E1103/NEO/R/F	E1103/NEO/GO/F	E1103/NEO/B/F	E1103/NEO/G/F	E1103/NEO/P/F
E1104/NEO/BLK/F	E1104/NEO/W/F	E1104/NEO/R/F	E1104/NEO/GO/F	E1104/NEO/B/F	E1104/NEO/G/F	E1104/NEO/P/F
E1105/NEO/BLK/F	E1105/NEO/W/F	E1105/NEO/R/F	E1105/NEO/GO/F	E1105/NEO/B/F	E1105/NEO/G/F	E1105/NEO/P/F
E1106/NEO/BLK/F	E1106/NEO/W/F	E1106/NEO/R/F	E1106/NEO/GO/F	E1106/NEO/B/F	E1106/NEO/G/F	E1106/NEO/P/F

Plain Neodymium Pot Magnet with Swivel Hooks

No.	Product Image	Diameter (mm)	Pot Height (mm)	Height incl. Hook (mm)	Hook Length (mm)	Pull Force (kg)	Pack QTY
1		25	15	65	55	18	PK2
2		32	15	65	55	30	PK2
3		36	15	65	55	40	PK2
4		40	15	65	55	50	PK2

Plain
E1070/NEO/F
E1071/NEO/F
E1072/NEO/F
E1073/NEO/F

Coloured Neodymium Pot Magnet with Swivel Hooks

No.	Product Image	Diameter (mm)	Pot Height (mm)	Height incl. Hook (mm)	Hook Length (mm)	Pull Force (kg)	Pack QTY
1		25	15	65	55	18	PK2
2		32	15	65	55	30	PK2
3		36	15	65	55	40	PK2
4		40	15	65	55	50	PK2

Black	White	Red	Gold	Blue	Green	Purple
E1070/NEO/BLK/F	E1070/NEO/W/F	E1070/NEO/R/F	E1070/NEO/GO/F	E1070/NEO/B/F	E1070/NEO/G/F	E1070/NEO/P/F
E1071/NEO/BLK/F	E1071/NEO/W/F	E1071/NEO/R/F	E1071/NEO/GO/F	E1071/NEO/B/F	E1071/NEO/G/F	E1071/NEO/P/F
E1072/NEO/BLK/F	E1072/NEO/W/F	E1072/NEO/R/F	E1072/NEO/GO/F	E1072/NEO/B/F	E1072/NEO/G/F	E1072/NEO/P/F
E1073/NEO/BLK/F	E1073/NEO/W/F	E1073/NEO/R/F	E1073/NEO/GO/F	E1073/NEO/B/F	E1073/NEO/G/F	E1073/NEO/P/F

Rubber Coated Ferrite Pot Magnet with Swivel Hooks

No.	Product Image	Diameter (mm)	Pot Height (mm)	Height incl. Hook (mm)	Hook Length (mm)	Pull Force (kg)	Pack QTY
1		36	14.5	62	52	4.2	PK2
2		52	14.5	62	52	7.4	PK1

Black	White
E1070/BLK/F	E1070/W/F
E1071/BLK/F	E1071/W/F

Rubber Coated Neodymium Pot Magnet with Swivel Hooks

No.	Product Image	Diameter (mm)	Pot Height (mm)	Height incl. Hook (mm)	Hook Length (mm)	Pull Force (kg)	Pack QTY
1		38	12.5	55	45	30	PK2

Black
E1060/NEO/BLK/F

Plastic Neodymium Pot Magnet with Swivel Hooks

No.	Product Image	Diameter (mm)	Pot Height (mm)	Hook Length (to the centre) (mm)	Pull Force (kg)	Pack QTY
1		53	43.5	65	2.5	PK1
2		68	51	65	10	PK1

Black	Orange	Yellow	Blue	Green	Purple
E1080/NEO/BLK/F	E1080/NEO/O/F	E1080/NEO/Y/F	E1080/NEO/B/F	E1080/NEO/G/F	E1080/NEO/P/F
E1081/NEO/BLK/F	E1081/NEO/O/F	E1081/NEO/Y/F	E1081/NEO/B/F	E1081/NEO/G/F	E1081/NEO/P/F

Silical Gel Neodymium Pot Magnet with Hook

No.	Product Image	Diameter (mm)	Thickness (mm)	Height incl. Hook (mm)	Pull Force (kg)	Pack QTY
1		45	25.5	75	50	PK1

Red
E1086/NEO/R/F

Rubber Coated Ferrite Magnet with 2 Hooks

No.	Product Image	Diameter (mm)	Pot Height (mm)	Hook Length (to the centre) L1/L2 (mm)	Pull Force (kg)	Pack QTY
1		58	26.5	53 / 83	11	PK1

Blue
E1080/B/F

Magnetic Wall Pin Set



No.	Product Image	Magnet Diameter (mm)	Magnet Thickness (mm)	Pull Force (kg)	Pack QTY
1		10	5	2.7	PK10

Standard
MWPS/F

Neodymium Channel Magnets



No.	Product Image	Length (mm)	Height (mm)	Width (mm)	Countersunk Hole	Pull Force (kg)	Pack QTY
1		10	5	13.5	1 x M3	4	PK5
2		20	5	13.5	1 x M3	8	PK5
3		40	5	13.5	2 x M3	17	PK3
4		60	5	13.5	2 x M3	30	PK3
5		80	5	13.5	2 x M3	35	PK1
6		100	5	13.5	2 x M3	37	PK1
7		120	5	13.5	2 x M3	42	PK1

Plain
NCM010F
NCM020F
NCM040F
NCM060F
NCM080F
NCM100F
NCM120F

Magnetic Trays

No.	Product Image	Diameter (mm)	Length (mm)	Width (mm)	Overall Height (mm)	Bowl Depth (mm)	Pack QTY
1		100	N/A	N/A	32	19	PK1
2		150	N/A	N/A	36	22	PK1
3		N/A	240	140	42	28	PK1
4		N/A	360	160	38	23	PK1
5		N/A	290	270	38	26	PK1

Standard
E634F
E633F
MT2414F
MT3616F
MT2927F