

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0369210302

Status:

Active

Overview:

L1NK Connector System

Description:

L1NK 396-to-L1NK 396 Off-the-Shelf (OTS) Cable Assembly, 3.96mm Pitch, Single Row, 150.00mm Length, 3 Circuits, Black



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	36921
Assembly Configuration	Dual Ended Connectors
Connector to Connector	L1NK 396-to-L1NK 396
Overmolded	No
Overview	L1NK Connector System
Product Name	L1NK 396
Type	Discrete Wire Assembly
UPC	193264110711
Physical	
Cable Length	150.00mm
Circuits (Loaded)	3
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	12.127/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.12mm
Wire Size AWG	18
Wire/Cable Type	UL 1015
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	369210300-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/88/2018 (15	
January 2019)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

36921 Series

Mates With

L1NK 396 Headers [207478](#) , [207479](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION