

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0369200601](#)
Status: **Active**
Overview: [Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems](#)
Description: [Pico-EZmate-to-Pico-EZmate Off-the-Shelf \(OTS\) Cable Assembly, 1.20mm Pitch, Single Row, 100.00mm Length, 6 Circuits, Black](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	36920
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Pico-EZmate-to-Pico-EZmate
Overmolded	No
Overview	Pico-EZmate and Pico-EZmate Slim Wire-to-Board Connector Systems
Product Name	Pico-EZmate
Type	Discrete Wire Assembly
UPC	193264110568

Physical

Cable Length	100.00mm
Circuits (Loaded)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	1.344/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.20mm
Plating min - Mating	0.100µm
Plating min - Termination	0.100µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.60-0.70mm
Wire Size AWG	28
Wire/Cable Type	UL 1571


Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	369200600-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[36920 Series](#)

Mates With

PicoEZmate Header [78171](#)