




NOTE: silver aluminium hoods with black cable

1. CABLE: NON-UL, NON-FOIL, 28AWG*4C (RED/YELLOW/GREEN/BLACK)
BLACK COLOR, OD=2.6±0.05mm, TPU JACKET.
2. LENGTH: 0.15M.
3. CONNECTORS: TYPE(C) M*1PCS (SHELL NICKEL).
3.5F*1PCS (SHELL NICKEL).
4. MOLD: MOLDING USB TYPE.
5. CONTACTS:




TYPE C	1	2	3	4
3.5 JACKET	1	2	3	64
	MIC	L	R	GND
	RED	YW	GR	BK

6. OPEN/SHORT TEST: 100% TEST.

A. 100% OPEN, SHORT & INTERMITTANCE TEST.

B. CONDUCTOR RESISTANCE: 3ohms MAX:

C. INSULATION RESISTANCE: 10MΩ/10ms:



1PCS/OPP BAG+LABEL

COMPANY	CDL	ITEM NO.	PSG91707	NO	B		SCALE	NON
REVISION	DATE	DISCRIPTION	DRAWN BY				UNIT(mm)	
REV.A/0	2019.06.25		DESIGNED BY				DRAWING NO.	
			APPROVAL BY					