




NOTE: silver aluminium hoods with black cable

- CABLE: NON-UL, NON-FOIL, 28AWG*4C (RED/YELLOW/GREEN/BLACK) BLACK COLOR, OD=2.6±0.05mm, TPU JACKET.
- LENGTH: 0.15M.
- CONNECTORS: TYPE(C) 24PIN*1PCS (SHELL NICKEL).
3.5F*1PCS (SHELL NICKEL).
- MOLD: MOLDING USB TYPE.
- CONTACTS:




TYPE C	1	2	3	4
3.5 JACKET	1	2	3	64
	MIC	L	R	GND
	RED	YW	GR	BK

- OPEN/SHORT TEST: 100% TEST.

A. 100% OPEN, SHORT & INTERMITTANCE TEST.

B. CONDUCTOR RESISTANCE: 3ohms MAX:

C. INSULATION RESISTANCE: 10MΩ/, 10ms:



1PCS/OPP BAG+LABEL

COMPANY	CDL		ITEM NO.	PSG91708		NO	B
REVISION	DATE	DISCRIPTION	DRAWN BY				
REV.A/0	2019.06.25		DESIGNED BY				
			APPROVAL BY				

PRO-SIGNAL

SCALE	NON
UNIT(mm)	
DRAWING NO.	