

## Category 6 24 Port UTP Patch Panel



### **Category 6 24 Port UTP Horizontal Patch Panel (SF24je)**

This Category 6 24 port patch panel is extremely well constructed and robust, offering the ideal platform for quick, easy LSA IDC terminations.

#### **Features**

- Performs to Category 6 standard (permanent link level)
- Robust and high quality metal construction
- Integral “tray type” horizontal IDC’s for ease of termination
- Accommodates LSA+ type termination tools
- Supplied with cage nut set.
- Printed with numbered ports and labelling facility
- T568A & T568B wiring options

#### **Specifications**

- Weight: 890g
- Dimensions: 483 x 44 x 98.5mm
- Colour: Black (RAL 9005)

- **Material:**
  - Frame: Galvanised cold rolled steel (1.2mm thickness)
  - RJ45 Contact: Nickel plated phosphor bronze with 50µ"/1.27µm gold plating

**Packaging:** Supplied in labelled white carton

**Commodity code:** 851777090

**EAN:** 5055386507570