


Part number

CX 02 GM



Brief description:

male insert, 2 poles, crimp connections, 100A 1000V, 8kV, 3, for male contacts 100A, 2 modules, modular units series MIXO

Product description		Approvals / Standards	
Model	male insert	Reference standard	EN 61984:2009-06
Version	Crimp connection	Quality mark	 DNV-GL, EAC
Product type	for male contacts 100A	General ordering information	
Family	MIXO series, customizable inserts	EAN13 code	8015747122818
Size	2 modules	Tariff number	85369095
N. of poles	2 poles	Packaging Information	
Technical data		Packaging length	112,00 mm
Current	100 A (A.C. and D.C.)	Packaging height	95,00 mm
Voltage	1000 V	Packaging width	117,00 mm
Rated impulse withstand voltage	8 kV	Packaging weight	0,19 kg
Pollution degree	3	Packaging volume	1,24 dm ³
Operating temperature range (min, max)	-40°C ... +125°C	Packaging description	Carton box
IP degree of protection	IP20 without enclosure, IP65/IP66/IP68/IP69 with enclosure	Packaging quantity	5 Pcs
Further technical details		Packaging EAN code	8015747122849
Characteristics according to EN 61984	100A 1000V 8kV 3 (100A 920/1600V 8kV 2)	Sub-packaging weight	0,04 kg
Insulation resistance	≥ 10 GΩ	Sub-packaging description	Plastic bag
Contact resistance	≤ 0,3 mΩ	Sub-packaging quantity	1 Pcs
Rated voltage according to UL/CSA	600V	Sub-packaging EAN barcode	8015747122856
UL 94 flammability rating	V-0		
Weight	28,80 g		

Part number



CX 02 GM





Catalogue drawings

Catalogue drawings

CX 02 GM



CX 02 GF



Notes

the modular inserts must be installed in suitable frames which in turn are installed in traditional housings or COB panel support