


LQW2BAS2N7J00#

"#" indicates a package specification code.



< List of part numbers with package codes >
 LQW2BAS2N7J00L , LQW2BAS2N7J00K , LQW2BAS2N7J00B

Shape



References

Packaging code	Specifications	Minimum quantity
L	φ180mm Embossed taping	2000
K	φ330mm Embossed taping	8000
B	Packing in bulk	500

Mass (Typ.)	
1 piece	0.014g

Specifications

Inductance	2.7nH ±5%
Inductance test frequency	250MHz
Rated current (Itemp) (Based on Temperature rise)	910mA
Max. of DC resistance	0.03Ω
Q (min.)	80
Q test frequency	1500MHz
Self resonance frequency (min.)	15000MHz
Operating temperature range (Self-temperature rise is not included)	-55°C to 125°C
Series	LQW2BAS_00

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.