
## 5x20mm fused terminal blocks

## **Product overview**

- 1 5 pole terminal strip with 5x20mm fuseholder
- Integral spare fuse carrier
- Interlocking fuseholder with CFTBN/1
- Anti rotation spigot
- IP20 finger protection
- Cable entry 4mm<sup>2</sup> (2.5mm<sup>2</sup> with wire protector)
- Wire protector on fuse terminal as standard
- · Wire protectors on earth pole to order
- **( E** approved
- EN60127 Fuseholders
- EN60998 Terminal blocks
- UL approved UL 1059





SPECIFICATION				
Rating	Fuseholder 250V AC Terminal 450V AC			
Current rating	Fuseholder 13A Terminal 20A			
Moulding	UL94-VO flame retardant PA			
Terminal	Brass, nickel plated			
Fuse clip	Phosphor bronze			
Wire protector	Stainless steel			
Temperature	-20° to 120°C			
Fuse size	5x20mm glass or ceramic			
Screws	Steel zinc plated M3, 0.5Nm			
GWIT	775°C			
GWFI	850°C			

PART NO.	BODY DIMENSIONS	FUSE WIRE PROTECTOR	M3 FIXING HOLE	FIXING SCREW & WASHERS	EARTH WIRE PROTECTED	WIRE PROTECTED TERMINALS
CFTBN/1	16.1 mm					
CFTBN/2	20.6 mm					
CFTBN/3	30.8 mm			•		
CFTBN/4	40.7 mm	•	•			
CFTBN/5	50.9 mm					
CFTBN/3NE	30.8 mm	•				
CFTBN/4NE	40.7 mm					
CFTBN/5NE	50.9 mm	•				
CFTBN/3NS	30.8 mm					
CFTBN/4NS	40.7 mm	•	•			
CFTBN/5NS	50.9 mm					
CFTBN/2WP	20.6 mm					
CFTBN/3WP	30.8 mm					
CFTBN/4WP	40.7 mm	•				
CFTBN/5WP	50.9 mm					
CFTBN/3EWP	30.8 mm	•	•			
CFTBN/4EWP	40.7 mm					
CFTBN/5EWP	50.9 mm					
CFTBN/3EWPG	30.8 mm					
CFTBN/4EWPG	40.7 mm	•				
CFTBN/5EWPG	50.9 mm					

## **ACCESSORIES**

Terminal cover

- · Screw/dust protection
- Easily cut to required size



PART NO.	POLES
CFTBN/3C	3 pole cover
CFTBN/5C	5 pole cover

## ASSOCIATED PRODUCTS

CFB0520F - Glass 5x20mm quick blow fuses page 228 CFB0520T - Glass 5x20mm time delay fuses page 228 CFB0521CF - Ceramic 5x20mm quick blow fuses page 229 - Ceramic 5x20mm time delay fuses CFB0521CT page 229

