

TECHNICAL SPECIFICATION

MODEL NO

A-1398

Bluetooth Music
Transceiver



SPECIFICATIONS :

1. No APP and driver need
2. Noise reduction and echo cancellation
3. Multi-band equalizer configuration
4. Support voice prompts
5. Integrated Li-type battery charger, support 30mA fast charge and over-discharge protection
6. Built AEC echo cancellation and noise cancellation circuit ANC.
7. Built-in enhanced signal transmission circuit, connected fast and stable
8. Automatic memory connected function, the operation is easier, more convenient



SPECIFICATIONS :

| | |
|----------------------------|---|
| Bluetooth Version | Bluetooth 4.2、 Consume low power (A2DP) |
| Supported protocol | A2DP, AVRCP, HFP, SPP HID |
| Current Consumption | ≤ 43MA (Receiving Mode) |
| | ≤ 60MA (Transmitting Mode) |
| | < 18MA (Standby Mode) |
| Built-in battery | Polymer 400MAH |
| Charging current | 300MA |
| Playing Period | 8 Hours |
| Bluetooth distance | 10M |
| Interface | Micro USB (For Charging) |
| | 3.5MM stereo audio port (For Transmitting and Receiving) |
| Compatibility | All Bluetooth audio devices. (smartphone/PC/ Notebook/Bluetooth phone., etc) |