

## DH350

Big Screen Entertainment









- Lights on viewing 3400 ANSI Lumens
- Amazing colour accurate Rec.709 colours
- Easy connectivity 2x HDMI, MHL, USB Power
- Clear, powerful audio 10W speaker

Convenient and easy to setup the bright and versatile DH350 boasts Amazing colour technology and conforms to Rec.709 delivering accurate true to life colour reproduction. This small projector is ideal for watching live sport, TV shows or movies any time of day on a big screen. You can even connect your games console and play games on it with its low input latency.



## **Specifications**

Opecinications	
Display/image	
Display technology	DLP
Resolution	1080p Full HD (1920x1080)
Brightness	3,400 lumens
Contrast ratio	22,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3
Keystone correction -	+/-40°
vertical	
Uniformity	80%
Screen size	0.71m ~ 7.65m (28" ~ 301") diagonal
Lamp info	
Light source type	Lamp
Lamp watts	240
Lamp life hours (up to)	3500 (Bright), 12000 (Dynamic), 10000 (Eco)
Optical	
Throw ratio	1.47:1 ~ 1.62:1
Projection distance (m)	1m - 9.8m
Zoom	1.1
Zoom type	Manual
Focal length (mm)	15.59 ~ 17.14
Native offset	116%
Connectivity Connections	
Connections	Inputs 1 x HDMI 1.4a 3D support + MHL, 1 x HDMI 1.4a 3D support
	Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A
	Control 1 x 3D sync, 1 x 12V trigger
	Control 1 x 3D sync, 1 x 12v trigger
General	05.40
Noise level (typical)	25dB
PC compatibility	FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p,
	576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Side-by-Side:1080i50 / 60, 720p50 / 60 Frame-pack:
	1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi,
	Finnish, French, German, Greek, Hungarian, Indonesian,
	Italian, Japanese, Norwegian, Polish, Portuguese, Romanian,
	Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish, Vietnamese
Operating conditions	5°C ~ 40°C, Max. Humidity 85%, Max. Altitude 3000m
Remote control	Backlit home remote
Speaker count	1
Watts per speaker	10W
In the box	AC power cord, remote control, Battery, basic user manual
Optional wireless models	HDCast Pro, QuickCast Bundle, QuickCast starter kit,
	WHD200
Power	
Power supply	100 ~ 240V, 50 ~ 60Hz
Power consumption	0.5W
(standby)	
Power consumption (min)	205W
Power consumption (max)	295W
Weight and dimensions	
Net weight	2.87kg
Dimensions (W x D x H) mm	316 x 244 x 108



