

Hot air tool

HL Stick

EAN 4007841 004019

STEINEL[®]
Intelligent technology



CE



VDE

Function description

Hands free. Compact hot air gun HL Stick for heating with pinpoint precision, ideal for craft and model-making. Practical, easy to grip and lightweight, hand-held and self-resting tool in one, sensational standing stability, with integrated LED work light, includes 4 attachment nozzles. red dot design award: The HL Stick was given the red dot product design award 2013 for its design.

Technical specifications

Output	350 W	Cord length	2.2 m
Temperature	400 – 500 °C	Dimensions (L x W x H)	235 x 78 x 76 mm
Airflow rate	100 – 100 l/min	Mains power supply	220 – 230 V / 50 Hz
Motor, type	Brush motor	PU1, net weight	0,594 kg
Heating element	Ceramic heating element	Manufacturer's Warranty	3 years
Function, hanger	Yes	PU1, EAN	4007841004019
Thermal cut-out	Yes		

Accessories

EAN 4007841 002886	Reduction nozzle 7 mm
EAN 4007841 077358	Reduction nozzle with reflector guard
EAN 4007841 077556	Reflector nozzle 10 mm
EAN 4007841 077655	Reflector nozzle 40 mm