

Data sheet

Hot air tool

HG 2320 E

Folding box

EAN 4007841007386



Function description

Precision digital control. Electronically controlled HG 2320 E hot air tool. 2300 W, digital temperature setting by joystick from 80 – 650 °C, temperature indicated in 10 °C steps on LCD display. Airflow regulation in 2 stages of 150 and 500 l/min.

Technical specifications

Output	2300 W
Temperature	80 – 650 °C
Airflow rate	150 – 500 l/min
Motor, type	Brush motor
Temperature setting	in 10°C steps by joystick
Temperature display	LCD display
Heating element	Ceramic heating element
Loc function	Yes
Residual heat indicator	Yes
Function, hanger	Yes
Restart protection	Yes
Thermal cut-out	Yes
Thermostat	Yes
Cord length	3 m
Dimensions (L x W x H)	253 x 87 x 200 mm
Mains power supply	230 V / 50 – 60 Hz
Model	Folding box
PU1, net weight	1,024 kg
Manufacturer's Warranty	1 year

Data sheet



Hot air tool

HG 2320 E

Folding box

EAN 4007841007386

Technical specifications

PU1, EAN

4007841007386
