

Hot air tool

HG 2320 E

Folding box

EAN 4007841 007386

STEINEL[®]
PROFESSIONAL



Function description

Precision digital control. Electronically controlled HG 2320 E hot air tool. 2300 W, digital temperature setting by joystick from 80 – 650 °C, temperature indicated in 10 °C steps on LCD display. Airflow regulation in 2 stages of 150 and 500 l/min.

Technical specifications

| | |
|-------------------------|---------------------------|
| Output | 2300 W |
| Temperature | 80 – 650 °C |
| Airflow rate | 150 – 500 l/min |
| Motor, type | Brush motor |
| Temperature setting | in 10°C steps by joystick |
| Temperature display | LCD display |
| Heating element | Ceramic heating element |
| Loc function | Yes |
| Residual heat indicator | Yes |
| Function, hanger | Yes |

| | |
|-------------------------|--------------------|
| Restart protection | Yes |
| Thermal cut-out | Yes |
| Thermostat | Yes |
| Cord length | 3 m |
| Dimensions (L x W x H) | 253 x 87 x 200 mm |
| Mains power supply | 230 V / 50 – 60 Hz |
| Model | Folding box |
| PU1, net weight | 1,024 kg |
| Manufacturer's Warranty | 1 year |
| PU1, EAN | 4007841007386 |

Hot air tool

HG 2320 E

Folding box

EAN 4007841 007386

STEINEL[®]
PROFESSIONAL

Accessories

| | |
|--------------------|---|
| EAN 4007841 074616 | Soldering reflector nozzle 10 mm |
| EAN 4007841 034566 | HL Tool Stand |
| EAN 4007841 010294 | Sieve reflector nozzle 50 x 35 mm T421 T399: T827 |
| EAN 4007841 009571 | Reduction nozzle 6 mm |
| EAN 4007841 075569 | 12-piece hot-air accessory kit |
| EAN 4007841 070618 | Reduction nozzle 9 mm |
| EAN 4007841 073114 | PVC plastic welding rod |
| EAN 4007841 006648 | Crimp connectors - Ø 1.5 - 2.5 mm |
| EAN 4007841 072766 | Shrink tubing III - ? 4,0 – 12,0 mm |
| EAN 4007841 006662 | Crimp connectors - Ø 0.1 - 6.0 mm |
| EAN 4007841 071318 | Shrink tubing I - ? 1,6 – 4,8 mm |
| EAN 4007841 006655 | Crimp connectors - Ø 0.5 - 1.5 mm |
| EAN 4007841 070717 | Reduction nozzle 14 mm |
| EAN 4007841 006785 | Pressure roller 40mm - Silicone |
| EAN 4007841 074210 | ABS plastic welding rod |
| EAN 4007841 009601 | Flexible hot air tool stand with suction pad foot |
| EAN 4007841 071417 | Shrink tubing II - ? 4,8 – 9,5 mm |
| EAN 4007841 070212 | Surface nozzle 75 mm |
| EAN 4007841 075811 | Shrink tubing kit |
| EAN 4007841 010317 | Paint Scraper Set |
| EAN 4007841 070915 | Welding nozzle |
| EAN 4007841 009625 | HL Light |
| EAN 4007841 070113 | Surface nozzle 50 mm |
| EAN 4007841 070311 | Window nozzle 50 mm |
| EAN 4007841 014919 | Temperature scanner HL Scan |
| EAN 4007841 070519 | Reflector nozzle |
| EAN 4007841 009595 | Flexible hot air tool stand with magnetic foot |
| EAN 4007841 034122 | Pressure roller 40mm - Teflon |
| EAN 4007841 073411 | PP plastic welding rod |
| EAN 4007841 070410 | Window nozzle 75 mm |
| EAN 4007841 071219 | HDPE plastic welding rod |
| EAN 4007841 093211 | Pressure roller 50mm - Rubber |
| EAN 4007841 074715 | Wide-slit nozzle |
| EAN 4007841 078218 | Fine dust filter HL 1920 E - HG 2320 E |
| EAN 4007841 053963 | Hot Air Tool Guard Cage HL 1820 S - HG 2320 E |