

Hot air tool

HL 1620 S

EAN 4007841 351106

STEINEL[®]
Intelligent technology



CE



VDE

Function description

The all-rounder. The two-speed HL 1620 S hot air tool soon becomes indispensable. Ideal for drying plasterwork, shrinking on cable sleeves, thawing frozen water pipes, stripping paint, waxing skis and snowboards and much more besides. With two temperature settings: 300° and 500° C.

Technical specifications

Output	1600 W
Temperature	300 – 500 °C
Airflow rate	240 – 450 l/min
Motor, type	Brush motor
Temperature setting	2-stage
Heating element	Micanite heating element
Residual heat indicator	No
Thermal cut-out	Yes

Thermostat	No
Cord length	2.2 m
Dimensions (L x W x H)	252 x 86 x 200 mm
Mains power supply	220 – 230 V / 50 – 60 Hz
PU1, net weight	0,671 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841351106

Hot air tool

HL 1620 S

EAN 4007841 351106



Accessories

EAN 4007841 034566	HL Tool Stand
EAN 4007841 006648	Crimp connectors - Ø 1.5 - 2.5 mm
EAN 4007841 072766	Shrink tubing III - ? 4,0 – 12,0 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm
EAN 4007841 071318	Shrink tubing I - ? 1,6 – 4,8 mm
EAN 4007841 006655	Crimp connectors - Ø 0.5 - 1.5 mm
EAN 4007841 071417	Shrink tubing II - ? 4,8 – 9,5 mm
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 070519	Reflector nozzle
EAN 4007841 070410	Window nozzle 75 mm