

TELEDATA ELECTRONIC SERVICE CASE

The case with a basic equipment of special tools for the installation and maintenance of complex telecommunication systems and data networks.

6700 **BERNSTEIN** TELEDATA with tool set

6715 **BERNSTEIN** TELEDATA without tool set

Description:

Case made from deep-drawn, impact-resistant, grained black plastic, with sturdy aluminium frame, dustproof and rainproof, acid- and scratch-resistant. 80 tools are clearly arranged on two removable tool trays, one of it on both sides, and in the plastic tray with adjustable partitions in the bottom of the case. The basic equipment for special operations at telecommunication systems and data networks may efficiently be completed by special tools additionally recommended.

The case has 2 locks.

Outside dimensions: 470 x 340 x 170 mm

Weight without tools: approx. 4.600 kg

Weight with tools: approx. 8.700 kg

Tool set

No.	Description of individual tools	No.	Description of individual tools
2-265	2 test prods , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire	6-103	Socket wrench 4.5 mm, chrome vanadium, chrome-plated, with square handle
2-601	IC-tweezers , nickel-plated, 125 mm, for gripping, inserting and removing IC's	6-104	Socket wrench 5.0 mm, chrome vanadium, chrome-plated, with square handle
2-620	PLCC-extractor	6-105	Socket wrench 5.5 mm, chrome-vanadium, chrome-plated, with square handle
2-701	Insertion tool with sensor for connecting the wires and simultaneously cutting off the residual wire	6-500-12	Double open-ended wrench , 12 x 13 mm, chrome vanadium, chrome-plated
3-112-2	Side cutters , 120 mm, for soft wire up to 1.0 mm, with rounded head, double leaf spring, chrome-plated, with red insulation	6-500-18	Double open-ended wrench , 18 x 19 mm, chrome vanadium, chrome-plated
3-134 VDE	Side cutters , 160 mm, for steel wire up to 1.6 mm Ø, chrome-plated, with VDE safety insulation	6-600	Combination ring- and open-ended wrench , 7-piece set, chrome vanadium, chrome-plated, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 13.0 mm
3-235-1	Telephon pliers , 145 mm, chrome-plated, with BERNSTEINIT-insulation	6-600-12	Combination ring- and open-ended wrench , 12 mm, chrome vanadium, chrome-plated
3-532-1	Flat nose pliers , 160 mm, with long jaws, chrome-plated, with BERNSTEINIT-insulation	6-600-17	Combination ring- and open-ended wrench , 17 mm, chrome vanadium, chrome-plated
3-585-1	Quick-action water pump pliers , 175 mm, made from chrome vanadium, chrome-plated, with BERNSTEINIT-insulation	6-600-19	Combination ring- and open-ended wrench , 19 mm, chrome vanadium, chrome-plated
3-732-1	Combination pliers , 160 mm, chrome-plated, with BERNSTEINIT-insulation	6-880	Hexagon wrench keys , 8-piece set, in a wallet, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
3-0605	Combination crimping pliers , 200 mm, for connector types 6P/6C, 6P/4C, 6P/2C, 8P/8C	6-950	Ballpoint wrench keys , hexagon, 8-piece set, in a wallet, 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0 mm
4-222	Screwdriver with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 260 x 3.0 mm, with black tip	6-995	Torx screwdrivers with bore-hole in the tip , 8-piece set, in a box, T 9, T 10, T 15, T 20, T 25, T 27, T 30, T 40
4-227	Crosspoint-screwdriver , size 1, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 300 mm, with black tip	7-425	Duster
4-228	Crosspoint-screwdriver , size 2, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 300 mm, with black tip	7-506	Roller tape measure , 2 m
4-431	Retaining screwdrivers for inserting and tightening slotted screws, blade made from chrome vanadium, nickel-plated, insulated, 100 x 3.0 mm	7-616	Pocket saw , with adjustable wooden handle, in a wallet
4-437	Retaining screwdriver for inserting and tightening cross-recess screws size 1 blade made from chrome vanadium, nickel-plated, insulated	9-316/5	5 Chip-Container , conductive box with lid, black, internal dimensions: 118 x 32 x 14 mm
5-107	Engineer's tweezers , made from steel, with bent tips, 150 mm, nickel-plated	14-601 VDE	Screwdriver with VDE-insulation, blade 75 x 2.5 mm
5-117	Engineer's tweezers , made from steel, straight-flat-wide, 145 mm, nickel-plated	14-602 VDE	Screwdriver with VDE-insulation, blade 100 x 3.5 mm
5-240	Warding files , 6-piece set, with wooden handles, in plastic wallet	14-603 VDE	Screwdriver with VDE-insulation, blade 100 x 4.0 mm
5-505	Insulation stripping tool for cable diameter of 8 up to 28 mm	14-631 VDE	Cross-recess screwdriver , size 0, with VDE-insulation, blade length 60 mm
		14-632 VDE	Cross-recess screwdriver , size 1, with VDE-insulation, blade length 80 mm
		14-633 VDE	Cross-recess screwdriver , size 2, with VDE-insulation, blade length 100 mm
		14-634 VDE	Cross-recess screwdriver , size 3, with VDE-insulation, blade length 150 mm

TELEDATA 6700 ELECTRONIC SERVICE CASE

The service case for the ambitious Telecommunication engineer

