Magnetic Proximity Sensors (Reed)

MP2019 Sensors

Reed based magnetic proximity sensor in plastic flange-mount package



Description

The MP2 Series sensors are reed position sensors. Normally open or closed contacts change states when a magnetic field is applied. The sensors act as non-latching electrical switches.

Features

- · Contacts hermetically sealed for long life
- Zero power consumption
- Suitable for DC and AC circuits
- Flange mount
- RoHS compliant
- IP65
- Operate/Release Distances*: 10.16 mm 22.86 mm (0.4" 0.9")

Typical Applications

- Door position & interlock
- Limit switch
- Flow/speed
- Home security
- Pedal switch

Environmental Specifications

| Vibration | 20 g 10 Hz to 1 kHz (MP201901), 20 g 10 Hz to 55 Hz (MP201902, M201903) |
|-----------------------|--|
| Operating Temperature | -40 °C to 105 °C (-40 °F to 221 °F) |
| Storage Temperature | -40 °C to 105 °C (-40 °F to 221 °F) |
| Ingress Protection | IP65 |

Electrical Specifications

| Typical Operating Time | 1 ms |
|--------------------------------------|--------------------|
| Breakdown Voltage | 200 VDC min. |
| Switching Voltage and Current | See Products chart |
| Contact Resistance and Power rating: | See Products chart |

Mechanical Specifications


| Housing Material | Glass-reinforced plastic |
|---|-----------------------------------|
| Operate/Release Distances* *with AS201901 magnetic actuator | 10.16 mm – 22.86 mm (0.4" – 0.9") |

Products

| Part Number | Contact Form | Maximum Power Rating | Maximum Switching Voltage | Maximum Switching Current | Maximum Contact Resistance |
|-------------|-------------------|-------------------------|------------------------------|------------------------------|-------------------------------|
| MP201901 | SPST-NO Form A | 10 W | 175 VAC/VDC | 0.5 A | 0.200 Ω |
| MP201902 | SPST-NC Form B | 3 W | 30 VAC/VDC | 0.2 A | 0.100 Ω |
| MP201903 | SPST-NC Form C | 3 W | 30 VAC/VDC | 0.2 A | 0.100 Ω |

All MP2019 sensors come with leads 24 AWG x 305 mm (12")










Dimensions mm (inches)

MP201901 (Form A - N.O.) and MP201902 (Form B - N.C.)




MP201903 (Form C - SPDT Changeover)





MAGNETIC ACTUATOR AS201901



ALNICO 8 MAGNET, VALOX 420 SEO CAPSULE

www.cherryswitches.com

