

# **Product Specification Sheet**



### 12W

VT-612SQ 12W LED PREMIUM PANEL WITH SAMSUNG CHIP COLORCODE:3000K SQUARE

Lumens 1000

Beam Angle 120

Dimensions ?170x170x12mm

Warm White SKU:709









## **Technical Information**

Output Voltage:	DC:24-48V
Watts:	12
Lumens:	1000
Shape:	Square
Beam Angle:	120
Cutting Size:	?160x160mm
Unit Color:	White
Body Type:	Aluminium
Long life:	30 000 Hours

 LED Chip Type:
 SMD

 IP Rating:
 IP20

 Dimmable:
 No

 Warranty (Years):
 5

 PF:
 >0.6

 CRI:
 >80

 Operation Temperature:
 -20°C to 45°C

 Input Power:
 AC:85-265V,50/60Hz

 Sensor Compatibility:
 Yes

## **Features**

Contemporary & Elegant Design

Highly Efficient LED Samsung Chip

Easy to install - Plug & Play

High-quality power driver ensures a reliable lifetime

Controlled Glare rating values for comfortable commercial applications

No Lead or Mercury content hence Environment-friendly

Easy to install & Low Maintenance

Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc





Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### **Unit Details**

 Gross Weight(GW) Kgs
 0.375

 Unit CBM
 0.00137

## Master Box Packaging

 Master Box Qty (Pcs Per Carton)
 20

 Qty Per Pallet
 1000

## **Listing Details**

 EAN Code
 3800157641654

 Commodity Code
 9405403990





OUR PRODUCTS ARE CURRENTLY SOLD IN OVER 70 COUNTRIES