



24W

VT-624RD 24W LED PREMIUM PANEL WITH SAMSUNG CHIP
COLORCODE:4000K ROUND

Lumens 2000	Beam Angle 120	Dimensions ø300x12mm
-----------------------	--------------------------	--------------------------------

Day White
SKU:725

5 YEARS
WARRANTY



SENSOR
COMPATIBLE



Technical Information

Output Voltage: DC:54-100V

Watts: 24

Lumens: 2000

Shape: Round

Beam Angle: 120

Cutting Size: ø280mm

Unit Color: White

Body Type: Aluminium

Long life: 30,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 5

PF: >0.9

CRI: >80

Operation Temperature: -20°C to 45°C

Input Power: AC:85-265V,50/60Hz

Sensor Compatibility: Yes

Features

- ✓ Contemporary & Elegant Design
- ✓ Highly Efficient LED Samsung Chip
- ✓ Easy to install - Plug & Play
- ✓ High-quality power driver ensures a reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ No Lead or Mercury content hence Environment-friendly
- ✓ Easy to install & Low Maintenance
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.88
Unit CBM	0.00433

Listing Details

EAN Code	3800157641814
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	300

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES