

* Kit No. EKDMGN011-KIT
Inductor
Content DFE322512F,DFE252010F/10P/12F/12P,DFE201610P/12P/12E/10E

No.	P/N	Full P/N	QTY
1	DFE322512F-R47M	DFE322512F-R47M=P2	10
2	DFE322512F-1R0M	DFE322512F-1R0M=P2	10
3	DFE322512F-1R5M	DFE322512F-1R5M=P2	10
4	DFE322512F-2R2M	DFE322512F-2R2M=P2	10
5	DFE322512F-3R3M	DFE322512F-3R3M=P2	10
6	DFE322512F-4R7M	DFE322512F-4R7M=P2	10
7	DFE322512F-100M	DFE322512F-100M=P2	10
8	DFE252010F-100M	DFE252010F-100M=P2	10
9	DFE252010F-1R0M	DFE252010F-1R0M=P2	10
10	DFE252010F-1R5M	DFE252010F-1R5M=P2	10
11	DFE252010F-2R2M	DFE252010F-2R2M=P2	10
12	DFE252010F-3R3M	DFE252010F-3R3M=P2	10
13	DFE252010F-4R7M	DFE252010F-4R7M=P2	10
14	DFE252010F-R33M	DFE252010F-R33M=P2	10
15	DFE252010F-R47M	DFE252010F-R47M=P2	10
16	DFE252010P-1R0M	DFE252010P-1R0M=P2	10
17	DFE252010P-1R5M	DFE252010P-1R5M=P2	10
18	DFE252010P-2R2M	DFE252010P-2R2M=P2	10
19	DFE252010P-4R7M	DFE252010P-4R7M=P2	10
20	DFE252010P-R33M	DFE252010P-R33M=P2	10
21	DFE252010P-3R3M	DFE252010P-3R3M=P2	10
22	DFE252010P-R47M	DFE252010P-R47M=P2	10
23	DFE252012F-100M	DFE252012F-100M=P2	10
24	DFE252012F-1R0M	DFE252012F-1R0M=P2	10
25	DFE252012F-1R5M	DFE252012F-1R5M=P2	10
26	DFE252012F-2R2M	DFE252012F-2R2M=P2	10
27	DFE252012F-3R3M	DFE252012F-3R3M=P2	10
28	DFE252012F-4R7M	DFE252012F-4R7M=P2	10
29	DFE252012F-R33M	DFE252012F-R33M=P2	10
30	DFE252012F-R47M	DFE252012F-R47M=P2	10
31	DFE252012P-1R0M	DFE252012P-1R0M=P2	10
32	DFE252012P-1R5M	DFE252012P-1R5M=P2	10
33	DFE252012P-2R2M	DFE252012P-2R2M=P2	10
34	DFE252012P-3R3M	DFE252012P-3R3M=P2	10
35	DFE252012P-4R7M	DFE252012P-4R7M=P2	10
36	DFE252012P-R33M	DFE252012P-R33M=P2	10
37	DFE252012P-R47M	DFE252012P-R47M=P2	10
38	DFE201610P-R24M	DFE201610P-R24M=P2	10

39	DFE201610P-R33M	DFE201610P-R33M=P2	10
40	DFE201610P-R47M	DFE201610P-R47M=P2	10
41	DFE201610P-1R0M	DFE201610P-1R0M=P2	10
42	DFE201610P-1R5M	DFE201610P-1R5M=P2	10
43	DFE201610P-2R2M	DFE201610P-2R2M=P2	10
44	DFE201612P-R24M	DFE201612P-R24M=P2	10
45	DFE201612P-R33M	DFE201612P-R33M=P2	10
46	DFE201612P-R47M	DFE201612P-R47M=P2	10
47	DFE201612P-1R0M	DFE201612P-1R0M=P2	10
48	DFE201612P-1R5M	DFE201612P-1R5M=P2	10
49	DFE201612P-2R2M	DFE201612P-2R2M=P2	10
50	DFE201612E-R24M	DFE201612E-R24M=P2	10
51	DFE201612E-R33M	DFE201612E-R33M=P2	10
52	DFE201612E-R47M	DFE201612E-R47M=P2	10
53	DFE201612E-1R0M	DFE201612E-1R0M=P2	10
54	DFE201612E-1R5M	DFE201612E-1R5M=P2	10
55	DFE201612E-2R2M	DFE201612E-2R2M=P2	10
56	DFE201612E-4R7M	DFE201612E-4R7M=P2	10
57	DFE201610E-R24M	DFE201610E-R24M=P2	10
58	DFE201610E-R33M	DFE201610E-R33M=P2	10
59	DFE201610E-R47M	DFE201610E-R47M=P2	10
60	DFE201610E-1R0M	DFE201610E-1R0M=P2	10
61	DFE201610E-1R5M	DFE201610E-1R5M=P2	10
62	DFE201610E-2R2M	DFE201610E-2R2M=P2	10
63	DFE201610E-4R7M	DFE201610E-4R7M=P2	10
64	DFE201610E-100M	DFE201610E-100M=P2	10
65			
66			
67			
68			
69			
70			
71			
72			