



**24W**

VT-2407 24W LED PREMIUM PANEL COLORCODE:4000K ROUND

Lumens  
**2000**

Beam Angle  
**120**

Dimensions  
**Ø300x12mm**

Day White  
SKU:4873

**2** YEARS  
WARRANTY

**SENSOR**  
COMPATIBLE



## Technical Information

Instant Start: 0-100% in 11s

Watts: 24

Lumens: 2000

Shape: Round

Beam Angle: 120

Cutting Size: 280mm

Unit Color: White

Body Type: Aluminium

Long life: 20,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No

Warranty (Years): 2

PF: >0.9

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:85-265V,50/60Hz

Sensor Compatibility: Yes

## Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note:



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.853
Length(Box)mm	375
Width(Box)mm	305
Height(Box)mm	35
Unit CBM	0.004186125

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	10
Qty Per Pallet	360

### Listing Details

EAN Code	3800157601566
Commodity Code	9405403990



READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES