



36W

VT-6237 36W LED PANEL 600x600 COLORCODE:4000K

Lumens
3240

Beam Angle
120

Dimensions
595x595mm

Day White
SKU:8084

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Output Voltage: **DC:30-42V**

Watts: **36**

Lumens: **3240**

Shape: **Square**

On/Off Cycles: **>10000**

Beam Angle: **120**

Output Current: **860mA**

Unit Color: **White**

Body Type: **Aluminium + PS + PP**

Long life: **20,000 Hours**

LED Chip Type: **SMD**

IP Rating: **IP20**

Dimmable: **No**

Warranty (Years): **2**

PF: **>0.9**

CRI: **>80**

Operation Temperature: **-20°C to +40°C**

Input Power: **AC:220-240V,50/60Hz**

Sensor Compatibility: **Yes**

Features

- ✓ Compare with incandescent, it can save over 80% electric cost
- ✓ Contemporary & Elegant Design
- ✓ Higher Light Transmission Rate
- ✓ Easy to install - Plug and play version
- ✓ Dimmable options available
- ✓ High quality power driver ensures reliable lifetime
- ✓ Controlled Glare rating values for comfortable commercial applications
- ✓ Range of Sizes to suit different workspaces
- ✓ Instant Start - 0-100% in
- ✓ No flickering, No U.V Radiation
- ✓ No Lead or Mercury content hence Environment friendly
- ✓ Application - Office, Conference Room, Showroom, Lobby, Cabin, Kitchen etc

Note:



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	2.918333
Unit CBM	0.01044

Listing Details

EAN Code	3800157646932
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	6
---------------------------------	---

READY STOCKS IN

UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES