



10W

VT-830 10W LED WALL LIGHT COLORCODE:6400K BLACK BODY 25CM HEIGHT

Lumens
450

Beam Angle
72

Dimensions
108x250mm

Day White
SKU:8324

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

Watts: **10**

Lumens: **450**

Beam Angle: **72**

Unit Color: **Black**

Body Type: **Aluminium**

Long life: **20,000 Hours**

LED Chip Type: **COB(CREE)**

IP Rating: **IP65**

Dimmable: **No**

Warranty (Years): **2**

PF: **>0.5**

CRI: **>80**

Operation Temperature: **-20 to +45°C**

Input Power: **AC:100-240V,50/60Hz**

Sensor Compatibility: **Yes**

Features

- ✓ Modern Wall lights available in sleek and stylish designs.
- ✓ Excellent heat dissipation
- ✓ Available in different color options - Warm White and Day White
- ✓ Easy installation and Maintenance
- ✓ Application: Perfect for halls, pathways, Bedroom, Kitchen etc



Note:

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	1.16
Unit CBM	0.00972

Listing Details

EAN Code	3800157632355
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	8
Qty Per Pallet	160

READY STOCKS IN

UK & EU



Dispatch within

24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES