

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1601052001**
Status: **Active**
Overview: MX150 Sealed and Unsealed Connector System
Description: MX150 Mat-Sealed Female Connector Assembly, Single Row, 2 Circuits, UL 94V-0, Keying Option A, without Connector Position Assurance, Black

Documents:

Drawing (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
Product Specification PS-160074-0001-001 (PDF)	Application Specification AS-33472-100-FR-001 (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	<u>160105</u>
Application	Power, Wire-to-Board, Wire-to-Wire
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	<u>MX150 Sealed and Unsealed Connector System</u>
Polarization	A
Product Name	MX150
UPC	889056677639

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	7.754/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33472-100-FR-001
Product Specification	PS-160074-0001-001
Sales Drawing	SD-160105-0002-001, SD-33471-0001-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

160105 Series

Mates With

160106 Male Single Row Sealed Connector

Use With

MX150 Female Terminal 33012 , 33001

MX150 Sealed Receptacle Cavity Plug 343454001