

Fabric label sheet - BMK 20X 8 WH CUS - 0824231

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Fabric label sheet, can be ordered: Sheet, white, labeled according to customer specifications, mounting type: adhesive, lettering field size: 20 mm x 8 mm, Number of individual labels: 270



Your advantages

- Available in various dimensions
- Self-adhesive labels for labeling by hand or with a plotter
- Labeling service: Phoenix Contact can custom-label all BMK ... markers according to your requirements
- Secure adhesion even on curved or uneven surfaces as well as round corners



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 351096
GTIN	4046356351096
Weight per Piece (excluding packing)	9.000 g
Custom tariff number	49119900
Country of origin	Poland
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	8 mm
Width (a)	20 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	white
Base element material	Polyester foil

Fabric label sheet - BMK 20X 8 WH CUS - 0824231

Technical data

General

Components	Silicone-free
Flammability rating according to UL 94	V0
Material	Polyester foil
Number of individual labels	270
Adhesive	Acrylic
Printability	Plotter
Device	5144615 CMS-P1-PLOTTER
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Result of weather resistance test	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result of wipe resistance test	Test passed
Marking mounting type	adhesive

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27400629

ETIM

ETIM 3.0	EC000761
----------	----------

Fabric label sheet - BMK 20X 8 WH CUS - 0824231

Classifications

ETIM

ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504