

## Shock protection - EMPPR (27X18) - 0829536

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Shock protection, Sheet, transparent, unlabeled, mounting type: snapped into marker carrier, lettering field size: 27 x 18 mm



### Your advantages

- High level of mechanical and chemical stability
- Suitable for permanent outdoor use
- Stuck or snapped onto labeled CARRIER ... to protect the labeling
- Extremely thick, yet flexible and transparent shock protection

### Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 614948
GTIN	4046356614948
Weight per Piece (excluding packing)	0.180 g
Custom tariff number	39204910
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	18 mm
Width (a)	27 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
---------------------------------	------------------

#### General

Color	transparent
Components	Silicone-free

## Shock protection - EMPPR (27X18) - 0829536

### Technical data

#### General

Flammability rating according to UL 94	V0
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	snapped into marker carrier

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

#### ETIM

ETIM 4.0	EC002848
ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504