


Plastic label - US-EMLP (27X18) YE - 0828895

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, lettering field size: 27 x 18 mm, Number of individual labels: 21



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 558990 |
| GTIN | 4046356558990 |
| Weight per Piece (excluding packing) | 18.900 g |
| Custom tariff number | 39199080 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|---------|
| Length (b) | 17.6 mm |
| Width (a) | 26.9 mm |
| Height (c) | 0.5 mm |

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

General

| | |
|--|---------------|
| Color | yellow |
| Components | Silicone-free |
| Flammability rating according to UL 94 | V0 |
| Material | PVC |

Plastic label - US-EMLP (27X18) YE - 0828895

Technical data

General

| | |
|---|-------------------------------------|
| RoHS compliant | Yes |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 21 |
| Number of individual labels per row | 3 |
| Adhesive | Acrylic |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Result of weather resistance test | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result of wipe resistance test | Test passed |
| Foil strength | 500 µm |
| Adhesive strength | 50 µm |
| Marking mounting type | adhesive |

Standards and Regulations

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V0 |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |
|------------|---|

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27400629 |
| eCl@ss 4.0 | 24190200 |
| eCl@ss 4.1 | 24190200 |
| eCl@ss 5.0 | 27149100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27149100 |
| eCl@ss 7.0 | 27149129 |
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
|----------|----------|

Plastic label - US-EMLP (27X18) YE - 0828895

Classifications

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |
| ETIM 7.0 | EC001288 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

Accessories

Accessories

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards

Marker carriers

Marker carriers - CARRIER-EMP 22 (27X18) - 0827448



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 18 mm

Plastic label - US-EMLP (27X18) YE - 0828895

Accessories

Marker carriers - CARRIER-EMLP 22 (27X18) - 0828987



Marker carriers, black, unlabeled, mounting type: screw, rivet, diameter: 22 mm, lettering field size: 27 x 18 mm
