

## Replacement die - CF 500/DIE AI-TWIN 10 - 1212262

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die for crimping machine CF 500, for TWIN ferrules (AI-TWIN...) 2 x 4, 2 x 6 and 2 x 10 mm<sup>2</sup>



### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356449861
Weight per Piece (excluding packing)	68.400 g
Custom tariff number	84799070
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Cable diameter	2.4 mm ... 3.7 mm
----------------	-------------------

#### General

Compression	WM crimp
Max. cross section	4 mm <sup>2</sup>
	6 mm <sup>2</sup>
	10 mm <sup>2</sup>
Min. cross section	4 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>

### Classifications

#### eCl@ss

eCl@ss 10.0.1	17139201
---------------	----------

# Replacement die - CF 500/DIE AI-TWIN 10 - 1212262

## Classifications

### eCl@ss

eCl@ss 4.0	21043000
eCl@ss 4.1	21043000
eCl@ss 5.0	21059000
eCl@ss 5.1	21059000
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 8.0	21049090
eCl@ss 9.0	17139201

### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

## Replacement die - CF 500/DIE AI-TWIN 10 - 1212262

### Approvals

EAC



RU C-  
DE.AI30.B.01549

### Accessories

#### Accessories

#### Cover

Covering hood - CF 500/COV AI TWIN - 1212266



Protective cover for crimping machine CF 500, for TWIN ferrules 2 x 4 - 2 x 10 mm<sup>2</sup> (AI-TWIN...)