


Replacement die - CRIMPFOX-C120 R25-50/DIE - 1212324

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



pre-round die (pair), for CRIMPFOX-C120, for sector cable 25 + 50 mm²

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454704
GTIN	4046356454704
Weight per Piece (excluding packing)	164.800 g
Custom tariff number	82079091
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

General

Color	black
Compression	Oval crimp
Min. cross section	25 mm ²
Max. cross section	50 mm ²
AWG min	3
AWG max	1/0
Min. cross section	25 mm ²
Max. cross section	50 mm ²

Classifications

eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300

Replacement die - CRIMPFOX-C120 R25-50/DIE - 1212324

Classifications

eCl@ss

eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------