


## Replacement die - CRIMPFOX-C120 RCT 70-1/DIE - 1212319

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die (pair), for CRIMPFOX-C120, for copper tube lug 10 + 70 mm<sup>2</sup>, WM crimp

### Key Commercial Data

|                                      |                                                                                                       |
|--------------------------------------|-------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                  |
| GTIN                                 | <br>4 046356 454650 |
| GTIN                                 | 4046356454650                                                                                         |
| Weight per Piece (excluding packing) | 135.800 g                                                                                             |
| Custom tariff number                 | 82079091                                                                                              |
| Country of origin                    | Germany                                                                                               |

### Technical data

#### General

|                    |                    |
|--------------------|--------------------|
| Color              | black              |
| Compression        | HEX crimp          |
| Type of contact    | CU conduit lugs    |
| Min. cross section | 10 mm <sup>2</sup> |
| Max. cross section | 70 mm <sup>2</sup> |
| AWG min            | 7                  |
| AWG max            | 2/0                |
| Min. cross section | 10 mm <sup>2</sup> |
| Max. cross section | 70 mm <sup>2</sup> |

### Classifications

#### eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 21019290 |
| eCl@ss 4.0    | 21040300 |
| eCl@ss 4.1    | 21040300 |
| eCl@ss 5.0    | 21040300 |
| eCl@ss 5.1    | 21040300 |

# Replacement die - CRIMPFOX-C120 RCT 70-1/DIE - 1212319

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 6.0 | 21043800 |
| eCl@ss 7.0 | 21043811 |
| eCl@ss 8.0 | 21043811 |
| eCl@ss 9.0 | 21019290 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC001282 |
| ETIM 5.0 | EC001282 |
| ETIM 6.0 | EC001282 |
| ETIM 7.0 | EC001282 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 27112118 |
| UNSPSC 7.0901 | 27111518 |
| UNSPSC 11     | 23171604 |
| UNSPSC 12.01  | 27111518 |
| UNSPSC 13.2   | 27111518 |
| UNSPSC 19.0   | 27111518 |

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

|     |                                                                                     |                          |
|-----|-------------------------------------------------------------------------------------|--------------------------|
| EAC |  | RU x-<br>DE.xx08.B.02974 |
|-----|-------------------------------------------------------------------------------------|--------------------------|