


## Replacement die - CRIMPFOX-M 25/DIE - 1212081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for ferrules 16 - 25 mm<sup>2</sup>, packed in a serial storage box

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 454513
GTIN	4046356454513
Weight per Piece (excluding packing)	86.000 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

#### General

Color	black
Compression	Trapezoidal crimp
Type of contact	Ferrules
Designation	Crimping position 1
Max. cross section	16 mm <sup>2</sup>
AWG max	6
Designation	Crimping position 2
Max. cross section	25 mm <sup>2</sup>
AWG max	4
Weight	72 g
Min. cross section	16 mm <sup>2</sup>
Max. cross section	25 mm <sup>2</sup>

# Replacement die - CRIMPFOX-M 25/DIE - 1212081

## Classifications

### eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	--	--------------------------

