

Replacement die - CRIMPFOX-M RCI 2,5/DIE - 1212074

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for Crimpfox-M, for insulated cable lugs 0.5 - 1.5 mm² and 1.5 - 2.5 mm² (red, blue), packed in a serial storage box

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356452533
Weight per Piece (excluding packing)	74.200 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	114 mm
Width (a)	75 mm
Height (c)	25.5 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	22
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm ²
Max. cross section	2.5 mm ²
AWG min	16
AWG max	14
Weight	75 g

Replacement die - CRIMPFOX-M RCI 2,5/DIE - 1212074

Technical data

General

Min. cross section	0.5 mm ²
Max. cross section	2.5 mm ²

Classifications

eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

Approvals

Approvals

Approvals


EAC

Ex Approvals

Replacement die - CRIMPFOX-M RCI 2,5/DIE - 1212074

Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>