

## Replacement die - CRIMPFOX-M SR 6-2/DIE - 1212472

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die, for MC4 solar connectors, lateral entry, 2.5 - 6 mm<sup>2</sup>

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356526982
Weight per Piece (excluding packing)	70.000 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### General

Compression	B crimp
Min. cross section	2.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
Min. cross section	2.5 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>

### Classifications

#### eCl@ss

eCl@ss 10.0.1	21019290
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21019290

# Replacement die - CRIMPFOX-M SR 6-2/DIE - 1212472

## Classifications

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111518
UNSPSC 19.0	27111518

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

---