


## Label - MM-TMT (EX6,35)R C1 WH/BK - 0803982

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Label, continuous, cassette, transparent with black imprint, mounting type: snap-on, can be marked with THERMOFOX

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 212562
GTIN	4055626212562
Weight per Piece (excluding packing)	45.000 g
Custom tariff number	96121010
Country of origin	China

### Technical data

#### Dimensions

Length (b)	5.5 m
Width (a)	6.35 mm

#### Ambient conditions

Ambient temperature (operation)	-5 °C ... 49 °C
---------------------------------	-----------------

#### General

Color	white
Type	flat
Components	free from silicone, halogen, and cadmium
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	snap into universal marker groove

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Label - MM-TMT (EX6,35)R C1 WH/BK - 0803982

### Technical data

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27141137

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC000761
ETIM 7.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131505
UNSPSC 19.0	39131505
UNSPSC 20.0	39131505
UNSPSC 21.0	39131505