

Hose clamp - WP-BASE HF 29 - 3240971


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Hose clamps



Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710893
GTIN	4046356710893
Weight per Piece (excluding packing)	19.210 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Hole diameter	6.5 mm
Diameter	29 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	silver/black
Components	halogen-free
Material	Steel, galvanized

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Hose clamp - WP-BASE HF 29 - 3240971

Classifications

eCl@ss

eCl@ss 10.0.1	23159090
eCl@ss 4.0	23150100
eCl@ss 4.1	23150100
eCl@ss 5.0	23159000
eCl@ss 5.1	23159000
eCl@ss 6.0	23159000
eCl@ss 7.0	23159090
eCl@ss 8.0	23159090
eCl@ss 9.0	23159090

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000127
ETIM 5.0	EC000127
ETIM 6.0	EC000127
ETIM 7.0	EC000127

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	31162906
UNSPSC 18.0	31162906
UNSPSC 19.0	31162906
UNSPSC 20.0	31162906
UNSPSC 21.0	31162906