

Stripping tool - WIREFOX-MP VDE - 1212528

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Multifunction stripping tool, for removing the jacket from cables with a diameter of 8 to 13 mm, for stripping cables with a cross section of 0.2 to 10 mm², with full-fledged diagonal cutter, VDE 1000 V AC/1500 V DC tested

Your advantages

WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 589567
GTIN	4046356589567
Weight per Piece (excluding packing)	240.500 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	190 mm
Cable diameter	8 mm ... 13 mm
Stripping length	100 mm

General

Color	black
Weight	230 g
Min. cross section	0.2 mm ²
Max. cross section	10 mm ²
AWG min	24
AWG max	8

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Stripping tool - WIREFOX-MP VDE - 1212528

Classifications

eCl@ss

eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	21040300
eCl@ss 6.0	21043700
eCl@ss 7.0	21043706
eCl@ss 8.0	21043706
eCl@ss 9.0	21043705

ETIM

ETIM 4.0	EC000163
ETIM 5.0	EC000163
ETIM 6.0	EC000163
ETIM 7.0	EC000163

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	27111510
UNSPSC 19.0	27111510

Approvals

Approvals

Approvals

VDE Zeichengenehmigung / EAC

Ex Approvals

Approval details

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	109845
------------------------	--	---	--------

Stripping tool - WIREFOX-MP VDE - 1212528

Approvals

EAC



RU x-
DE.xx08.B.02974