


## Insert label - PMST (10X38) GN - 0831081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Identification label for flow-through substances with centered hole for addition fixing with a pop rivet, for assembling the CARRIER-PMP (110x38), CARRIER/L-PMP (110x38) and CARRIER-PMP-ENCLOSED (110x38) according to DIN 2403



### Key Commercial Data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 941143
GTIN	4046356941143
Weight per Piece (excluding packing)	0.590 g
Custom tariff number	39199080
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	38 mm
Width (a)	10 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing.

#### General

Color	green
Components	Free from silicone and cadmium
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1

## Insert label - PMST (10X38) GN - 0831081

### Technical data

#### General

Number of individual labels per row	1
Marking mounting type	snapped into marker carrier

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 5.0	27149100
eCl@ss 5.1	27371300
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

#### ETIM

ETIM 5.0	EC001288
ETIM 6.0	EC001288
ETIM 7.0	EC001288

#### UNSPSC

UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504