

KEMET, MPXV, Power, 2200 nH, 20%

General Information

Series:	MPXV
Style:	SMD
Description:	Surface Mount Inductor
Features:	Power Inductors
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Core:	Composite
Miscellaneous:	40 (K) Temperature Rise Max.

Dimensions

L	10.8mm +/-0.3mm
W	10mm +/-0.2mm
T	5.4mm MAX
LL	2.2mm NOM
G	4.7mm +/-0.3mm

Packaging Specifications

Packaging:	T&R, 330mm
Packaging Quantity:	500

Specifications

Inductance:	2.2 uH (100 KHz)
Inductance Tolerance:	20%
Temperature Range:	-55/+155°C
Shielded:	Yes
Current:	18 A (Irms, 40C Rise By Self Heating), 12 A (Isat, 20% Drop In Inductance), 16.5 A (Isat, 30% Drop In Inductance)
DC Resistance:	5.41 mOhms
Self-Resonant Frequency:	21 MHz