



12W

VT-857 12W LED GARDEN LAMP COLORCODE:3000K BLACK BODY

Lumens
720

Beam Angle
30

Dimensions
73x255mm

Warm White
SKU:7544

2 YEARS
WARRANTY



Technical Information

Instant Start: 0-100% in

Watts: 12

Lumens: 720

On/Off Cycles: 15000

Beam Angle: 30

Unit Color: Black

Body Type: Aluminium

Long life: 20,000 Hours

LED Chip Type: SMD

IP Rating: IP65

Dimmable: No

Warranty (Years): 2

PF: >0.6

CRI: >80

Operation Temperature: -20 to +45°C

Input Power: AC:100-240V,50/60Hz

Features

- ✓ Perfectly designed IP65 rated garden spike with LED
- ✓ Works perfectly in extreme temperatures from -20° to +45° without any adverse etc
- ✓ Sturdily built with an Aluminium body
- ✓ Easy to Install and low maintenance
- ✓ Applications - Suitable for Gardens, Landscapes, Tree uplighting etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.46
Unit CBM	0.001224

Listing Details

EAN Code	3800157633444
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
Qty Per Pallet	1000

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES