



12W

VT-857 12W LED GARDEN LAMP COLORCODE:3000K WHITE BODY

Lumens  
**720**

Beam Angle  
**30**

Dimensions  
**73x255mm**

Warm White  
SKU:7547

**2 YEARS**  
WARRANTY



## Technical Information

Instant Start: 0-100% in

Watts: 12

Lumens: 720

On/Off Cycles: 15000

Beam Angle: 30

Unit Color: White

Body Type: Aluminium

Long life: 20,000 Hours

LED Chip Type: COB

IP Rating: IP65

Dimmable: No

Warranty (Years): 2

PF: >0.6

CRI: >80

Operation Temperature: -20 to +45°C

Input Power: AC:100-240V,50/60Hz

## Features

- ✓ Perfectly designed IP65 rated garden spike with LED
- ✓ Works perfectly in extreme temperatures from -20° to +45° without any adverse etc
- ✓ Sturdily built with an Aluminium body
- ✓ Easy to Install and low maintenance
- ✓ Applications - Suitable for Gardens, Landscapes, Tree uplighting etc



Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

# Packaging

## Unit Details

Gross Weight(GW) Kgs	0.46
Unit CBM	0.001224

## Listing Details

EAN Code	3800157633475
Commodity Code	9405403990

## Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
Qty Per Pallet	1000

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES